# HIGH BLAST TORCHES HBT SERIES

#### **FEATURES**

External construction: cast iron G25
 Internal pipe and orifices: AISI304
 Standard nozzle: cast iron G25

Heat capacity: from 12 to 850 kW
 Adequate to different types of gas: CH4/L.P./propane/etc.

• Air pressure required: from 1.4 bar to 8.4 bar

• Minimum gas pressure:

Coke-oven gas: 13 mbar
Natural gas: 7.6 mbar
L.P., propane, butane: 2.5 mbar

• Incorporated compressed air adjuster.

• Incorporated inspirated air adjuster.

• Low pressured air consumption: 10% of the quantity required

for combustion

#### **APPLICATIONS**

- Cupola firing.
- Core drying.
- Ladle and crucible melting reheating.
- Pouring spout heating.



#### **DESCRIPTION**

High blast torches are equipped with nozzle and venturi mixer. They use a small amount of high pressure air to pick up incoming gas at the mixer. Ten percent of the total air required is passed through a primary modified venturi which inspirates the gas flow and elevates its pressure. The suction effect allows for the use of low capacity

injectors because 90 % of the air required is inspirated from outside. The high pressure air valve and primary air shutter provide for wide ranges of adjustment. Injector type design of high pressure stage, prevents air feed back into the gas line.

**International Sales** 

## INSTALLATION

- Make high pressure air and gas connections. These may be pipe or flexible hoses.
- The connections should not be smaller than the valve size.
- Check air and gas lines for leaks.
- Loosen locknut on body and open primary air shutter wide.
- Open air valve full.
- Hold lighting torch alongside burner nozzle and slowly open gas cock.
- After flame is lit, flame is adjusted via modulation of the gas cock.
- Opening gas wider gives a softer, longer flame. Closing it slightly produces a sharper, shorter flame.
- Adjust air valve and primary air shutter to obtain the capacity required.

## **IGNITION AND FLAME DETECTION**

High blast torches are usually lighted through pilot flame which is taken away from the nozzle after lighting. Factory mounted spark electrode (WAND), UV-scanner (UV-2) and flame control (ESTRO) are

also available. A slow opening gas valve is absolutely essential in case of immediate ignition.

Catalog No.	Pilot burne	r electrode	Ignition electrode			
	Ignition	Detection	Ignition	Detection		
6 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
8 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
10 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
12 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
16 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
20 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
24 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		
32 HBT	P42PBST-W/X	Wand	Wand	Wand - UV/2 *		

(\*) In most cases, we suggest you to make flame detection through UV- scanner. In some particular cases, it is possible to use continue pilot burner with detection electrode.



# CAPACITY TABLE

Catalog no.		Capacity kW				Air flow Nm³/h 2,8 bar					Flame length (*) mm					
6 HBT		16				2					200 ÷ 300					
8 HBT		25				4					250 ÷ 350					
10 HBT		60				9.3					350 ÷ 400					
12 HBT		90				12.4					450 ÷ 500					
16 HBT		160				17					600 ÷ 650					
20 HBT		220				23.5					750 ÷ 800					
	24 HBT		270				29.4					900 ÷ 1.000				
	32 HBT		480				49					1.200 ÷ 1.300				
	Air pressure bar	1.4	1.76	2.1	2.46	2.8	3.16	3.5	3.86	4.2	4.56	4.9	5.6	6.7	7	8.4

Multiply gas and air capacities by factor for air pressure.

0.71

Factor


0.79 | 0.87 | 0.94 | 1.00 | 1.06 | 1.12 | 1.18 | 1.23 | 1.28 | 1.32 | 1.42 | 1.50 | 1.58 |



1.73

<sup>(\*)</sup> Flame lenght are approximate, referred to burner feeded with natural gas, <u>free air</u>, working at stoichiometric ratio and at nominal capacity.

# **DIMENSIONS**



Catalog no.	A npt	B npt	C npt	D mm	E mm	F mm	Mass kg
6 HBT	1/2"	3/8"	3/4"	375	130	85	2.3
8 HBT	1/2″	3/8"	1"	470	130	85	3
10 HBT	3/4"	3/8"	1.1/4"	570	150	90	4.3
12 HBT	3/4"	3/8"	1.1/2"	600	150	90	4.6
16 HBT	1"	3/8"	2″	715	190	100	9
20 HBT	1"	3/8"	2.1/2"	760	190	100	11.3
24 HBT	1.1/4"	3/8"	3″	970	200	110	18
32 HBT	1.1/4″	3/8"	4"	1190	220	110	27



NOTE: Based on the company's policy aimed at a continuous improvement on product quality, ESA-PYRONICS reserves the right to bring changes to the technical characteristics of this device without previous notice. Our catalog updated to the latest version is available on our web site www.esapyronics.com and it is possible to download modified documents